



BENCHTOP LOW SPEED CENTRIFUGE

LCE series centrifuges use centrifugal force to separate liquid and solid particles or components in liquid and liquid mixturesMachinery. Separate the solid particles from the liquid in the suspension; Separate two liquids of different densities from each other in an emulsion.

PRODUCT FEATURES

- ABS high strength shell, surface frosted, not easy to age, beautiful and light, and in line with ergonomics;
- LCD liquid crystal display, adjustable speed, time and other parameters, functional partition display, beautiful and clear ;
- DC brushless motor, low noise, maintenance free, high-speed bearing, stable operation;
- Multiple time settings, precise control, high work efficiency, multi-functional encoder adjustment, and barrier free function setting;
- With program preset function, it can save 5 different running programs ;



100-5000RPM
Speed



8*15ml/8*12ml
/8*10ml





10s~99min
59s



LCD Display



Simple operation

Product Model	LCH-LCF-05		LCH-LCF-05D	
Image				
Voltage v	AC100-240			
Power W	150			
Display	LED		LCD	
Speed Range rpm	100-5000			
Speed Control Accuracy rpm	±10			
Timing Range	10s~99min59s			
Motor Type	DC Brushless motor			
Max RCF xg	2795			
Tube Capacity	8*15ml/8*12ml/8*10ml			